

| 型式 | | T | d1 | d2 | 付属品 | 吸着力 N {kgf} | | 表面磁束密度 ガウス [G] | | ¥基準単価 | | | |
|-----------------------------|----|-----|-----|-----|--------|-----------------|-----------------|-----------------|-----------------|-------|--------|-------|--------|
| Type | A | | | | | NHXCC NHXCCH | NHXCS NHXCSH | NHXCC NHXCCH | NHXCS NHXCSH | NHXCC | NHXCCH | NHXCS | NHXCSH |
| (丸タイプ) NHXCC NHXCCH | 8 | 2 | 5.5 | 3.0 | M2.5-6 | 7.8 {0.8} | 10.8 {1.1} | 2000~2500 | — | 440 | 510 | 480 | — |
| | | 3 | | | | 10.8 {1.1} | 16.6 {1.7} | 2400~2800 | — | 440 | 510 | 480 | — |
| | 10 | 3 | 6.5 | 3.5 | M3-8 | 14.7 {1.5} | 22.5 {2.3} | 3500~4000 | — | 440 | 510 | 480 | — |
| | | 4 | | | | 18.6 {1.9} | 24.5 {2.5} | 4000~4200 | 3800~4000 | 440 | 510 | 480 | 600 |
| (正方形タイプ) NHXCS NHXCSH | 12 | 3 | 6.5 | 3.5 | M3-8 | 18.6 {1.9} | — | 3600~4000 | — | 580 | — | — | — |
| | | 4.5 | | | | 23.5 {2.4} | 27.4 {2.8} | 4100~4300 | 3900~4100 | 580 | 640 | 650 | 700 |
| | 15 | 3 | 9 | 4.8 | M4-10 | 23.5 {2.4} | — | 3800~4200 | — | 720 | — | — | — |
| | | 5 | | | | 41.1 {4.2} | 31.3 {3.2} | 4200~4500 | 4000~4300 | 720 | 800 | 820 | 880 |
| | 20 | 4 | 11 | 5.8 | M5-12 | 49 {5.0} | — | 3800~4100 | — | 900 | — | — | — |
| | | 5.5 | | | | 54.8 {5.6} | 44.1 {4.5} | 4200~4400 | 4000~4200 | 900 | 990 | 1,020 | 1,100 |
| | 25 | 4 | 13 | 7.0 | M6-15 | 58.8 {6.0} | — | 3700~4100 | — | 1,380 | — | — | — |
| | | 6 | | | | 78.4 {8.0} | 98.0 {10.0} | 4100~4400 | 3900~4300 | 1,380 | 1,420 | 1,520 | 1,560 |