

型式	d	密着長	Fmax.	N {kgf} Max.	Fa%	¥基準単価	
Type D-L							
UTT 10-	10	0.85	5.1	4	7.8 [0.8]	40	400
	15	0.85	5.1	6	11.8 [1.2]		
	20	1.0	9.5	8	15.7 [1.6]		
	25	1.0	9.5	10	19.6 [2.0]		
	30	1.1	14.3	12	23.5 [2.4]		
	35	1.1	14.3	14	27.5 [2.8]		
	40	1.2	11.4	16	31.4 [3.2]		
	45	1.2	11.4	18	35.3 [3.6]		
	50	1.2	11.4	20	39.2 [4.0]		
	60	1.3	29.9	24	47.1 [4.8]		
	70	1.4	43.4	24	47.1 [4.8]		
UTT 13-	15	1.0	5.75	6	11.8 [1.2]	40	480
	20	1.2	10.5	8	15.7 [1.6]		
	25	1.2	10.5	10	19.6 [2.0]		
	30	1.3	15	12	23.5 [2.4]		
	35	1.3	15	14	27.5 [2.8]		
	40	1.4	20.3	16	31.4 [3.2]		
	45	1.4	20.3	18	35.3 [3.6]		
	50	1.5	27.8	20	39.2 [4.0]		
	60	1.5	27.8	24	47.1 [4.8]		
	70	1.6	38.4	28	54.9 [5.6]		
	80	1.6	38.4	32	62.8 [6.4]		
UTT 16-	15	1.2	7.2	6	11.8 [1.2]	40	520
	20	1.3	9.1	8	15.7 [1.6]		
	25	1.3	9.1	10	19.6 [2.0]		
	30	1.4	12.3	12	23.5 [2.4]		
	35	1.5	16.5	14	27.5 [2.8]		
	40	1.6	21.6	16	31.4 [3.2]		
	45	1.6	21.6	18	35.3 [3.6]		
	50	1.7	28	20	39.2 [4.0]		
	60	1.7	28	24	47.1 [4.8]		
	70	1.8	36	28	54.9 [5.6]		
	80	1.8	36	32	62.8 [6.4]		
UTT 20-	20	1.7	10.6	8	31.4 [3.2]	40	600
	25	1.8	12.6	10	39.2 [4.0]		
	30	1.8	12.6	12	47.1 [4.8]		
	35	2.0	19	14	54.9 [5.6]		
	40	2.0	19	16	62.8 [6.4]		
	45	2.0	19	18	70.6 [7.2]		
	50	2.2	27.5	20	78.5 [8.0]		
	60	2.2	27.5	24	94.1 [9.6]		
	70	2.3	34.5	28	109.8 [11.2]		
	80	2.4	40.8	32	125.5 [12.8]		