

「L寸指定タイプ」の項目を訂正

訂正前

■L寸指定タイプ

D	L	¥基準単価				
		ストレート				
		ウレタン		シリコン		耐熱ウレタン
		ROFRUS	ROFRUA	ROFRGA ROFRHA	ROFRSS	ROFRTS
25	21~25	3,900	3,680	3,990	5,270	6,060
	26~49	4,270	3,990	4,340	5,750	6,200
30	21~25	4,320	4,050	4,400	5,490	6,920
	26~49	4,800	4,410	4,790	5,980	7,670
35	26~49	5,130	4,570	4,970	6,570	8,060
35A						
40	26~49	5,500	4,780	5,210	6,760	8,800
40A						
50	26~50	6,190	5,220	5,680	7,150	9,640
50A	51~99	6,860	5,650	6,160	8,300	11,210



訂正後

■L寸指定タイプ

D	L	¥基準単価				
		ストレート				
		ウレタン		シリコン		耐熱ウレタン
		ROFRUS	ROFRUA	ROFRGA ROFRHA	ROFRSS	ROFRTS
25	21~25	3,900	3,680	3,990	5,270	6,060
	26~49	4,270	3,990	4,340	5,750	6,200
30	21~25	4,320	4,050	4,400	5,490	6,920
	26~49	4,800	4,410	4,790	5,980	7,670
35	26~49	5,130	4,570	4,970	6,570	8,060
35A						
40	26~49	5,500	4,780	5,210	6,760	8,800
40A						
50	26~50	6,190	5,220	5,680	7,150	9,640
50A	51~99	6,860	5,650	6,160	8,300	11,210

<訂正用>

50  
50A