

表組の数値を訂正。

型式																¥基準単価						
Type	D	L	T	t	H	A	L ₁	d	d ₁	(D ₁)	(t ₁)	B	C	h	締付ボルト M	質量 g	SHFT	SHFM	SHFSS	SHF	SHFD	
D8~16-20~50 SHFT SHFM SHFSS	3	43	10	5	24	20	32	5.5	9	10	1.5	18	2	9.5	M4	32(11)	—	—	—	940	—	
	4															32(11)				940		
	5															32(11)				940		
	6															32(11)				940		
	8															29(10)				890		1,150
D3~50 SHF	10	47	13	7	28	25	36	7	10	20	2	18	2	9.5	M4	29(10)	890	1,150	1,490	860	1,050	
	12															52(18)	890	1,150	1,490	860	1,050	
	13															52(18)	890	1,150	1,490	860	1,050	
	15															64(22)	960	1,240	1,530	980	—	
D8~16-20~30 SHFD	16	60	20	8	31	28	40	7	10	24	2	22	2.5	M5	64(22)	960	1,240	1,530	900	1,100		
	18														110(38)	—	—	—	1,060	—		
	20														110(38)	1,080	1,430	1,670	980	1,190		
	25														179(62)	1,240	1,660	1,940	1,130	1,400		
	30														21	M6	278(96)	1,330	1,800	2,070	1,200	1,460
D8~16-20~30 SHFD	35	92	35	14	58	50	72	12	15	40	3	22	2.5	M8	25.5	350(121)	2,010	2,510	3,420	1,370	—	
	40														30	M10	500(173)	2,670	3,340	4,790	1,660	—
	50														38	M12	952(329)	4,170	4,830	7,260	2,230	—

<訂正用>

940
940
940
940
940
860
860
860
980
900
1,060
980
1,130
1,200
1,370
1,660
2,230