

P. 333

規格表内を変更

ロッド		材 質
外径選択タイプ	外径フリータイプ	
RDOF	—	SUS303
RDOS	FRDOS	SUS304
RDOH	—	SUS316
RDOA	—	A2017
RDOK	—	A5056
RD52A	—	A5052
RDOG	—	C3604-LCD (カドミウム低減黄銅)
RDOT	—	純チタン2種

<訂正用>

ロッド		材 質
外径選択タイプ	外径フリータイプ	
RDOF	—	SUS303
RDOS	FRDOS	SUS304
RDOH	—	SUS316
RDOA	—	A2017
RDOK	—	A5056
RD52A	—	A5052
RDOG	—	C3604-LCD (カドミウム低減黄銅)
RDOT	—	純チタン2種

P. 334

表内を変更

5	150	180
6	170	210
8	170	210
10	170	220
12	210	300
13	210	300
15	220	300
16	250	380
18	290	490
20	300	500
25	390	690

RDOA
(A2017)

5	150	200
6	160	210
8	160	210
10	160	220
12	200	290
13	200	290
15	210	290
16	240	370
18	290	480
20	290	480
25	390	670

RDOK
(A5056)

5	150	180
6	170	210
8	170	220
10	170	220
12	210	300
15	220	300
16	250	380
18	290	490
20	300	500
3	180	380

RD52A
(A5052)

<訂正用>

5	150	180
6	170	210
8	170	210
10	170	220
12	210	300
13	210	300
15	220	300
16	250	380
18	290	490
20	300	500
25	390	690

RDOA
(A2017)

<訂正用>

5	150	200
6	160	210
8	160	210
10	160	220
12	200	290
13	200	290
15	210	290
16	240	370
18	290	480
20	290	480
25	390	670

RDOK
(A5056)

<訂正用>

5	150	180
6	170	210
8	170	220
10	170	220
12	210	300
15	220	300
16	250	380
18	290	490
20	300	500
3	180	380

RD52A
(A5052)