

## P.1107 (規格表)

D寸法 公差部にかかる線を削除 (赤線部)

H	Df6		型 式		L 指定0.1mm単位	
			Type	D		
11	8	<del>-0.013</del>	<div style="border: 1px solid black; padding: 2px; display: inline-block;">ツバ厚4mm</div>  <b>RP4TL</b> (ツバ直角度：0.1)	8	35.0~250.0	
15	10	<del>-0.022</del>		10	35.0~300.0	
17	12	-0.016 -0.027		12	35.0~300.0	
18	13			13	35.0~300.0	
20	15			15	35.0~350.0	
21	16			16	35.0~350.0	
25	20	-0.020 -0.033		<b>RP4TV</b> (ツバ直角度：0.05)	20	50.0~400.0
30	25				25	50.0~450.0
35	30				30	50.0~450.0
37	32				-0.025 -0.041	32
15	10	-0.013 -0.022	<div style="border: 1px solid black; padding: 2px; display: inline-block;">ツバ厚8mm</div>  <b>RP8TI</b>	10	35.0~300.0	
17	12	-0.016 -0.027		12	35.0~300.0	
18	13			13	35.0~300.0	
20	15			15	35.0~350.0	