

## 赤枠内価格を修正

Catalog No.		¥単価											
Type	D	最短L 50	L51 100	L101 150	L151 200	L201 300	L301 400	L401 500	L501 600	L601 800	L801 1000	L1001 1200	L1201 1490
SFAF	8	530	800	1,060	1,330	1,610	1,870	2,340	2,800	3,740	—	—	—
	10	550	810	1,090	1,350	1,630	1,900	2,190	2,460	3,280	—	—	—
	12	560	840	1,120	1,390	1,700	2,000	2,290	2,580	3,910	4,500	—	—
	13	570	850	1,130	1,420	1,720	2,030	2,340	2,640	3,980	4,610	—	—
	15	930	1,390	1,850	2,320	2,640	2,950	3,270	3,590	4,960	5,590	—	—
	16	930	1,390	1,850	2,320	2,640	2,950	3,270	3,590	4,960	5,590	6,330	—
	18	950	1,420	1,890	2,360	2,700	3,030	3,370	3,700	5,110	5,780	6,450	—
	20	950	1,420	1,890	2,360	2,700	3,030	3,370	3,700	5,110	5,780	6,450	—
	25	1,020	1,530	2,040	2,550	2,970	3,390	3,820	4,250	5,820	6,670	7,520	10,260
	30	1,060	1,610	2,130	2,670	3,150	3,630	4,120	4,600	6,300	7,270	8,200	14,140
	35	1,360	2,060	2,740	3,410	4,120	4,820	5,530	6,240	8,550	9,900	11,310	16,420
40	1,490	2,240	2,990	3,730	4,600	5,450	6,310	7,170	9,740	11,470	13,150	20,670	
50	1,710	2,580	3,440	4,300	5,440	6,570	7,720	8,870	12,030	14,240	16,530	—	
SSFAF	8	830	1,240	1,650	2,060	2,670	3,290	4,110	4,930	6,570	—	—	—
	10	830	1,240	1,650	2,060	2,620	3,180	4,040	4,890	6,570	—	—	—
	12	940	1,410	1,870	2,340	2,870	3,400	4,220	5,050	6,730	8,880	—	—
	13	940	1,410	1,870	2,340	2,870	3,400	4,220	5,050	6,730	8,880	—	—
	15	1,080	1,620	2,160	2,700	3,150	3,600	4,490	5,370	7,130	8,940	—	—
	16	1,080	1,620	2,160	2,700	3,150	3,600	4,490	5,370	7,130	8,940	10,740	—
	18	1,280	1,930	2,560	3,200	3,700	4,180	5,160	6,130	8,100	10,060	11,990	—
	20	1,280	1,930	2,560	3,200	3,700	4,180	5,160	6,130	8,100	10,060	11,990	—
	25	1,380	2,070	2,750	3,440	3,990	4,530	5,640	6,750	8,940	11,150	13,420	—
	30	1,500	2,260	3,000	3,750	4,400	5,050	6,320	7,590	10,120	12,580	15,110	18,890
	35	1,750	2,630	3,510	4,390	5,570	6,770	8,120	9,470	12,500	15,210	17,920	22,410
40	2,160	3,250	4,330	5,410	6,870	8,330	10,000	11,670	15,440	18,770	22,120	27,660	
50	3,190	4,800	6,390	7,990	9,790	11,570	13,910	16,230	21,730	26,520	31,300	39,140	
RSFAF	8	1,350	1,620	1,940	2,270	2,610	2,990	3,580	—	—	—	—	—
	10	1,370	1,690	2,030	2,410	2,870	3,250	3,660	—	—	—	—	—
	12	1,440	1,840	2,240	2,630	3,110	3,650	4,170	—	—	—	—	—
	13	1,450	1,850	2,250	2,710	3,250	3,790	4,340	—	—	—	—	—
	15	1,930	2,510	3,140	3,850	4,460	5,130	5,800	—	—	—	—	—
	16	1,930	2,570	3,200	3,970	4,700	5,360	6,030	—	—	—	—	—
	18	2,010	2,710	3,420	4,240	5,050	5,850	6,450	—	—	—	—	—
	20	2,070	2,890	3,650	4,540	5,460	6,110	6,780	—	—	—	—	—
	25	2,430	3,410	4,390	5,350	6,380	7,320	8,200	—	—	—	—	—
	30	2,770	3,960	4,940	6,130	7,210	8,420	9,630	—	—	—	—	—
	PSFAF	8	670	1,010	1,350	1,680	2,180	2,670	3,340	4,000	5,340	—	—
10		670	1,010	1,350	1,680	2,140	2,590	3,300	3,990	5,330	—	—	—
12		770	1,150	1,520	1,910	2,350	2,780	3,440	4,110	5,480	7,240	—	—
13		770	1,150	1,520	1,910	2,350	2,780	3,440	4,110	5,480	7,240	—	—
15		890	1,330	1,770	2,210	2,570	2,920	3,650	4,370	5,810	7,290	—	—
16		890	1,330	1,770	2,210	2,570	2,920	3,650	4,370	5,810	7,290	8,740	—
18		1,050	1,570	2,090	2,610	3,000	3,400	4,200	4,990	6,600	8,190	9,770	—
20		1,050	1,570	2,090	2,610	3,000	3,400	4,200	4,990	6,600	8,190	9,770	—
25		1,120	1,680	2,230	2,800	3,260	3,700	4,600	5,490	7,290	9,080	10,920	—
30		1,230	1,840	2,440	3,060	3,590	4,110	5,140	6,170	8,230	10,230	12,300	14,770
35		1,640	2,470	3,280	4,110	4,960	5,800	6,650	7,500	10,290	11,900	13,610	16,340
40	1,800	2,700	3,600	4,500	5,530	6,570	7,590	8,610	11,720	13,810	15,790	18,970	
50	2,070	3,100	4,130	5,160	6,540	7,920	9,290	10,660	14,470	17,140	19,880	23,870	
PSSFAF	8	1,210	1,820	2,420	3,020	3,930	4,820	6,200	7,560	10,080	—	—	—
	10	1,210	1,820	2,420	3,020	3,850	4,660	5,920	7,190	9,580	—	—	—
	12	1,380	2,070	2,750	3,440	4,210	4,980	6,190	7,400	9,880	13,040	—	—
	13	1,380	2,070	2,750	3,440	4,210	4,980	6,190	7,400	9,880	13,040	—	—
	15	1,590	2,380	3,170	3,960	4,620	5,260	6,570	7,880	10,480	13,140	—	—
	16	1,590	2,380	3,170	3,960	4,620	5,260	6,570	7,880	10,480	13,140	15,770	—
	18	1,880	2,820	3,760	4,690	5,420	6,130	7,570	9,010	11,900	14,760	17,610	—
	20	1,880	2,820	3,760	4,690	5,420	6,130	7,570	9,010	11,900	14,760	17,610	—
	25	2,030	3,030	4,050	5,060	5,860	6,650	8,290	9,920	13,140	16,370	19,700	—
	30	2,200	3,310	4,410	5,510	6,450	7,400	9,270	11,140	14,860	18,480	22,180	27,730
	35	2,570	3,860	5,140	6,430	8,170	9,920	11,900	13,890	18,340	22,300	26,270	32,850
40	3,180	4,760	6,350	7,930	10,070	12,200	14,670	17,120	22,630	27,530	32,430	40,540	
50	4,690	7,020	9,370	11,700	14,340	16,970	20,380	23,800	31,850	38,890	45,910	57,380	

&lt;訂正用&gt;

15,110 18,890