

P.240 (規格表)

D25-15のY<sub>1</sub>寸訂正

型式		B 選択	D <sub>1</sub>	H	M (並目)	d	R	W	X	Y	Z	h	M <sub>1</sub> (並目)	Y <sub>1</sub>	P	¥単価 1~9コ								
Type	D															S <sub>CS</sub> NK	P <sub>CS</sub> NK	S <sub>CS</sub> NK	S <sub>CK</sub> NK S <sub>CJ</sub> NK	P <sub>SC</sub> NK P <sub>SC</sub> JNK	S <sub>SC</sub> NK S <sub>SC</sub> JNK	S <sub>CP</sub> NK	P <sub>SC</sub> PKNK	S <sub>SC</sub> PKNK
スタンダードタイプ S <sub>CS</sub> NK P <sub>CS</sub> NK S <sub>SC</sub> NK (D寸8~40)	6	8	20	17	M3	3.4	3	1	6	4	6~6.5					560	640	980	—	—	—	—	—	—
		10			M4	4.5	3.75									560	640	980	—	—	—	—	—	—
	8	8	25	19	M3	3.4	3	1.5	8	5	7~9					610	700	1,020	—	—	—	—	—	—
		10			M4	4.5	3.75									610	700	1,020	—	—	—	—	—	—
カット面取付穴タイプ S <sub>CK</sub> NK P <sub>SC</sub> KNK S <sub>SC</sub> KNK (D寸10~40)	10	8	30	22	M3	3.4	3	1.5	9	5	8~10				10	640	740	1,030	840	940	1,230	1,360	1,420	2,300
		*10			M4	4.5	3.75									640	740	1,030	870	940	1,230	1,360	1,420	2,300
	12	12	34	24	M5	5.5	4.5	1.5	10	6	9~10					670	740	1,100	—	—	—	—	—	—
		*10			M4	4.5	3.75									670	740	1,100	—	—	—	—	—	—
側面取付穴タイプ S <sub>C</sub> JNK P <sub>SC</sub> JNK S <sub>SC</sub> JNK (D寸10~40)	15	12	35	24	M5	5.5	4.5	1.5	11.5	6	10~11	5.6	M4	12	12	730	850	1,130	930	1,050	1,330	1,640	1,720	2,590
		*10														—	—	—	—	—	—	—	—	—
	16	12	40	30	M5	5.5	4.5	1.5	12	6	11~13	—	—	—	—	730	850	1,180	—	—	—	—	—	—
		*10														4.8	M5	12	12	730	850	1,130	930	1,050
セルレットカット面取付穴タイプ S <sub>CP</sub> KNK P <sub>SC</sub> PKNK S <sub>SC</sub> PKNK (D寸10~30)	20	*10	45	36	M5	5.5	4.5	1.5	14	7	13	6	M5	14	14	880	1,020	1,250	1,080	1,120	1,450	1,720	1,820	2,750
		12														—	—	—	—	—	—	—	—	—
	25	15	50	36	M6	6.6	6	1.5	15	8	13~15	—	—	—	—	1,000	1,100	1,570	—	—	—	—	—	—
		12														—	—	—	—	—	—	—	—	—
カト面取付穴タイプ、 側面取付穴タイプ、 セルレットカト面取 付穴タイプは、 8寸*印サイズのみ	30	*15	60	46	M6	6.6	6	1.5	17	7	16					980	1,100	1,620	—	—	—	—	—	—
		12														—	—	—	—	—	—	—	—	—
	35	15	70	53	M8	9	7	2	18	10	16~18	6.7	M5	16	16	1,050	1,130	1,800	1,150	1,200	1,820	1,900	1,920	3,220
		*15														7.2	M6	20	20	1,200	1,400	2,100	1,300	1,500
	40	18	70	53	M8	9	7	2	23	12	21	—	—	—	—	1,250	1,520	2,770	—	—	—	—	—	—
		*18														23	9	M8	26	26	1,450	1,700	3,650	1,600

① カット面取付穴タイプのD10のP寸法は8になります。

② カット面取付穴タイプのD10~16のM<sub>1</sub>有効ネジ深さは7mm(下穴貫通)、D20は9mm(下穴貫通)、その他についてはネジ貫通となっています。