

ベアリング 品番	シール	¥単価 1~9コ																	
		ラウンドタイプ						スクエアタイプ						コンパクトタイプ					
		BGRRB	BGRR	BARR	SBARR	SBAMRR	SBGRR	BGSRB	BGSR	BASR	SBASR	SBAMSR	SBGSR	BGCRB	BGCR	BACR	SBACR	SBAMCR	SBGCR
623		1,170	1,290	1,430	—	—	—	1,320	1,460	1,630	—	—	—	1,260	1,410	1,570	—	—	—
624		1,170	1,290	1,450	—	—	—	1,320	1,460	1,630	—	—	—	1,270	1,420	1,580	—	—	—
605		1,190	1,330	1,470	—	—	—	1,350	1,500	1,660	—	—	—	1,300	1,440	1,600	—	—	—
625		1,230	1,360	1,540	—	—	—	1,400	1,550	1,740	—	—	—	1,350	1,490	1,660	—	—	—
606		1,280	1,430	1,550	1,840	1,900	2,130	1,440	1,610	1,750	2,020	2,080	3,550	1,390	1,540	1,680	1,950	2,000	3,420
626		1,320	1,460	1,610	1,930	1,990	2,190	1,490	1,650	1,810	2,140	2,190	3,660	1,430	1,590	1,740	2,060	2,110	3,520
698		1,520	1,690	1,940	2,480	2,530	2,610	1,730	1,910	2,180	2,730	2,790	4,330	1,650	1,830	2,100	2,640	2,700	4,140
608		1,360	1,520	1,620	2,020	2,080	2,250	1,550	1,720	1,820	2,220	2,270	3,730	1,490	1,650	1,760	2,150	2,200	3,630
628		1,380	1,540	1,760	2,250	2,300	2,370	1,570	1,740	1,980	2,480	2,540	3,940	1,500	1,660	1,910	2,400	2,450	3,760
6800		1,800	2,000	2,240	2,650	2,710	3,080	2,020	2,260	2,510	2,940	3,000	3,450	1,960	2,180	2,390	2,820	2,870	3,310
6900		1,640	1,820	2,040	2,410	2,460	2,800	1,840	2,050	2,280	2,670	2,730	3,140	1,780	1,980	2,170	2,560	2,610	3,010
6000		1,430	1,590	1,780	2,270	2,380	2,560	1,620	1,810	2,000	2,550	2,640	2,890	1,560	1,730	1,920	2,420	2,520	2,780
6200		1,460	1,620	1,900	2,430	2,530	2,610	1,640	1,820	2,150	2,700	2,800	2,960	1,590	1,760	2,070	2,600	2,700	2,830
6801		1,850	2,060	2,340	2,730	2,840	3,180	2,070	2,290	2,620	3,010	3,110	3,550	1,990	2,210	2,520	2,900	3,030	3,440
6901		1,680	1,870	2,130	2,480	2,580	2,890	1,880	2,080	2,380	2,740	2,830	3,230	1,810	2,010	2,290	2,640	2,750	3,130
6001		1,470	1,630	1,900	2,400	2,500	2,660	1,670	1,850	2,150	2,660	2,760	3,000	1,600	1,780	2,070	2,570	2,670	2,890
6201	ZZ (×1.0)	1,510	1,670	1,930	2,480	2,580	2,800	1,700	1,890	2,190	2,740	2,830	3,170	1,630	1,810	2,090	2,630	2,740	3,050
6802		1,980	2,200	2,540	2,990	3,090	3,540	2,200	2,440	2,840	3,300	3,420	3,980	2,130	2,380	2,730	3,200	3,300	3,840
6902	VV (×1.1)	1,800	2,000	2,310	2,720	2,810	3,220	2,000	2,220	2,580	3,000	3,110	3,620	1,940	2,160	2,480	2,910	3,000	3,490
6002		1,590	1,770	2,000	2,600	2,730	2,990	1,810	2,000	2,240	2,890	3,010	3,390	1,730	1,920	2,160	2,790	2,920	3,260
6202	DD (×1.1)	1,620	1,810	2,080	2,720	2,840	3,090	1,830	2,040	2,350	2,980	3,110	3,490	1,760	1,960	2,260	2,890	3,010	3,350
6903		2,050	2,160	2,500	3,080	3,200	4,120	2,320	2,440	2,820	3,450	3,570	4,280	2,240	2,360	2,660	3,060	3,180	4,160
6003		1,870	1,970	2,260	3,320	3,440	3,870	2,110	2,220	2,560	3,690	3,810	4,350	2,030	2,140	2,360	3,300	3,420	3,910
6203		1,930	2,030	2,320	3,430	3,550	3,930	2,160	2,270	2,620	3,790	3,910	4,420	2,190	2,300	2,420	3,410	3,530	3,980
6804		2,410	2,530	2,870	3,530	3,670	4,610	2,680	2,830	3,220	3,890	4,050	5,140	2,600	2,730	3,080	3,760	3,890	5,010
6904		2,190	2,300	2,610	3,450	3,650	4,190	2,440	2,570	2,930	3,540	3,680	4,850	2,360	2,650	2,800	3,610	3,880	4,610
6004		1,910	2,010	2,320	3,140	3,440	3,940	2,160	2,270	2,620	3,460	3,760	4,460	2,080	2,190	2,530	3,340	3,650	4,280
6204		1,950	2,050	2,400	3,330	3,630	4,190	2,200	2,320	2,730	3,670	3,970	4,730	2,120	2,230	2,610	3,550	3,870	4,550
6805		2,200	2,310	—	—	—	—	2,490	2,620	—	—	—	—	2,380	2,500	—	—	—	—
6905		2,100	2,210	—	—	—	—	2,370	2,500	—	—	—	—	2,270	2,380	—	—	—	—
6005		1,970	2,070	—	—	—	—	2,210	2,330	—	—	—	—	2,140	2,250	—	—	—	—
6205		2,000	2,100	—	—	—	—	2,260	2,380	—	—	—	—	2,160	2,270	—	—	—	—
6806		2,620	2,760	—	—	—	—	2,960	3,110	—	—	—	—	2,850	3,000	—	—	—	—
6906		2,500	2,640	—	—	—	—	2,820	2,970	—	—	—	—	2,720	2,870	—	—	—	—
6006		2,340	2,460	—	—	—	—	2,650	2,790	—	—	—	—	2,550	2,680	—	—	—	—
6206		2,380	2,510	—	—	—	—	2,690	2,830	—	—	—	—	2,590	2,730	—	—	—	—
6007		2,840	2,990	—	—	—	—	3,200	3,370	—	—	—	—	3,100	3,260	—	—	—	—
6008		3,370	3,550	—	—	—	—	3,790	3,990	—	—	—	—	3,660	3,850	—	—	—	—

<訂正用>

4,190 | 2,440 | 2,570 | 2,930 | 3,540 | 3,680