


赤枠内数値を変更

Catalog No.			L	S	d	DH7	許容差	B	ℓ	H	W	T	dh	D1g7	許容差	P.C.D.	K	A	F	d1	d2	H1
Type	ベアリング品番	シール	選択																			
(ラウンドタイプ)	623	ZZ (両シールド)	20 30	5	3	10	$+0.015$ 0	4	2.65	33	16	7	7	14	-0.006 -0.024	24	27	24	—	6.5	3.5	3.1
	624		20 30	5	4	13	$+0.018$ 0	5	2.65	35	18		9	17		26	28	26				
	605		25 35	5		14		5	2.65	38	20		10	18		28	30	28				
	625		35 40	10	5	16		5	2.65	40	22		12	20		30	31	30				
	606		25 40	5		17	$+0.021$ 0	6	2.65	41	23	8	13	21	-0.007 -0.028	31	32	31				
	626		35 45	10	6	19		6	2.65	44	25		15	24		34	34	34				
	698		25 35	5		19		6	2.65	44	25		15	24		34	34	34				
	608		25 35	5	8	22		7	2.65	47	29		18	27		37	36	37				
	628		35 45	10		24	$+0.021$ 0	8	2.85	50	32		20	30	-0.009 -0.034	40	37	40				
(スクエアタイプ)	BGRZB	6800	20 30	5		19		5	2.65	44	25		15	24		34	34	34		8	4.5	4.1
	BGRZ	6900	25 40	5		22		6	2.65	47	29		19	27		37	36	37				
	BARZ	6000	35 50	10		26	$+0.025$ 0	8	2.85	52	34		22	32	-0.009 -0.034	42	39	42				
	SBARZ	6200	45 55	15		30		9	2.85	56	38		24	36		46	42	46				
	SBAMRZ	6801	25 35	5		21		5	2.85	47	29		17	26		37	36	37				
	SBGRZ	6901	35 50	10		24		6	2.85	50	31		21	30		40	38	40				
	6001	*VV (非接触 ゴムシール) DD (接触 ゴムシール)	35 50	10	12	28	$+0.021$ 0	8	2.85	54	36		24	34	-0.009 -0.034	44	40	44				
	6201		45 55	15		32		10	2.85	58	40		26	38		48	43	48				
	BGSZB		25 35	10		24		5	2.85	50	32		20	30		40	37	40				
	BGSZ		35 60	10		28		7	2.85	59	37		25	35		47	45	47				
	BASZ		45 65	15		32	$+0.025$ 0	9	2.85	62	40		28	38	-0.009 -0.034	50	46	50				
	SBASZ		50 65	15		35		11	3.75	66	44		29	42		54	49	54				
	SBAMSZ		45 55	15		30		7	2.85	60	38		27	36		48	46	48		9.5	5.5	5.1
	SBGSZ		50 65	15	17	35		10	3.75	66	44		31	42		54	50	54				
(コンパクトタイプ)	6203		60 70	20		40	$+0.025$ 0	12	3.95	72	50		34	48	-0.010 -0.040	60	54	60				
	BGCZB	6804	35 50	10		32		7	3.75	62	40		28	38		50	46	44				
	BGCZ	6904	50 65	15		37		9	3.75	72	47		34	45		59	54	54				
	BACZ	6004	60 70	20		42		12	3.95	77	54		36	50		64	59	56				
	SBACZ	6204	65 70	20		47	$+0.030$ 0	14	3.95	81	58		40	54	-0.010 -0.040	68	62	59		11	6.6	6.1
	SBAMCZ	6805	35 50	15		37		7	3.75	72	47		34	45		59	54	54				
	SBGCZ	6905	35 50	15		42		9	3.95	77	54		36	50		64	59	55				
	6005	60 80	20		47	12		3.95	88	58		41	54	-0.010 -0.040	72	67	63	14		9	8.1	
	6205	65 80	20		52	$+0.025$ 0	15	4.2	94	64		45	60		78	72	68					
	6806	35 50	15		42		7	3.95	77	54		36	50		64	59	56	11		6.6	6.1	
	6906	35 50	15		47		9	3.95	88	58		41	54		72	67	62					
	6006		60 80	20		55	$+0.030$ 0	13	4.2	96	66		48	62	-0.010 -0.040	80	73	70				
	6206		62 80	20		62		16	4.2	104	74		55	70		88	79	77		14	9	8.1
	6007		70 80	20	35	62		14	4.2	104	74		55	70		88	79	75				
	6008		80 90	25	40	68		15	5.2	114	82		60	78		96	86	80				

<訂正用>



① 適用サイズは価格表でご確認ください。② *VV (非接触ゴムシール) は623番・624番・605番・606番は選択できません。

1

2