

- ①ベアリング品番6008のS寸数値訂正
- ②注釈の削除と追加

型式			L	S	d	DH7	許容差	B	H	W	T	dh	D197	許容差	P.C.D.	K	A	F	d1	d2	H1
Type	ベアリング品番	シール	選択																		
	623		20 30	5	3	10	+0.015	4	33	16	7	7	14	-0.006	24	27	24		6.5	3.5	3.1
	624		20 30	5	4	13		5	35	18		9	17	-0.024	26	28	26				
	605		25 35	5		14	+0.018	5	38	20		10	18		28	30	28				
	625		35 40	10	5	16	0	5	40	22		12	20		30	31	30				
	606		25 40	5		17		6	41	23		13	21	-0.007	31	32	31		8	4.5	4.1
	626		35 45	10	6	19	+0.021	6	44	25		15	24	-0.028	34	34	34				
	678		20 30	5		12	+0.018	3.5	35	18		10	16	-0.006	26	28	26		6.5	3.5	3.1
	698		25 35	5		19		6	44	25		15	24		34	34	34				
	608		25 35	5	8	22	+0.021	7	47	29		18	27		37	36	37				
	628		35 45	10		24	0	8	50	32		20	30	-0.007	40	37	40				
	6700		20 30	5		15	+0.018	4	40	22		12	19	-0.028	30	31	30				
	6800		20 30	5		19		5	44	25		15	24		34	34	34				
(ラウンドタイプ)	6900		25 40	5	10	22	+0.021	6	47	29		19	27		37	36	37				
	BGRYB		35 50	10		26	0	8	52	34		22	32	-0.009	42	39	42				
	BGRY		45 55	15		30		9	56	38		24	36	-0.034	46	42	46		8	4.5	4.1
	BARY		20 30	5		18	+0.018	4	44	25		15	23		34	34	34				
	SBARY		25 35	5		21		5	47	29		17	26	-0.007	37	36	37				
	SBAMRY		35 50	10	12	24	+0.021	6	50	31		21	30	-0.028	40	38	40				
	SBGRY		35 50	10		28	0	8	54	36		24	34	-0.009	44	40	44				
	6201	ZZ (両シールド)	45 55	15		32	+0.025	10	58	40		26	38	-0.034	48	43	48				
(スクエアタイプ)	6702		25 35	10		21	+0.021	4	47	29		18	26	-0.007	37	36	37				
	BGSYB		25 35	10		24	+0.021	5	50	32		20	30	-0.028	40	37	40				
	BGSY	*VV (非接触)	35 60	10	15	28	0	7	59	37		25	35		47	45	47				
	B002	DD (ゴムシール)	45 65	15		32	+0.025	9	62	40		28	38		50	46	50		9.5	5.5	5.1
	6202		50 65	15		35	0	11	66	44		29	42		54	49	54				
	SBASYS		30 40	10		26	+0.021	5	52	34		22	32		42	39	42		8	4.5	4.1
	SBAMS		45 55	15		30	0	7	60	38		27	36		48	46	48				
	SBGSY		50 65	15	17	35	+0.025	10	66	44		31	42	-0.009	54	50	54		9.5	5.5	5.1
(コンパクトタイプ)	6203		60 70	20		40	0	12	72	50		34	48	-0.034	60	54	60				
	6704		30 40	10		27	+0.021	4	59	35		23	33		47	45	41	23	8	4.5	4.1
	BGCYB		35 50	10	32	32		7	62	40		28	38		50	46	44	24	9.5	5.5	5.1
	BGCY		50 65	15	20	37		9	72	47		34	45		59	54	54	24			
	BACY		60 70	20		42		12	77	54		36	50		64	59	56	32			
	6204		65 70	20		47	+0.025	14	81	58		40	54	-0.010	68	62	59	34	11	6.6	6.1
	SBACY		35 50	15		37	0	7	72	47		34	45	-0.009	59	54	54	24			
	SBAMCY		35 50	15	25	42		9	77	54		36	50	-0.034	64	59	55	32			
	SBGCY		60 80	20		47		12	88	58		41	54	-0.010	72	67	63	36			
	6805		65 80	20		52	+0.030	15	94	64		45	60	-0.040	78	72	68	39	14	9	8.1
	6905		35 50	15		42	+0.025	7	77	54		36	50	-0.009	64	59	56	32	11	6.6	6.1
	6005		35 50	15		47	0	9	88	58		41	54	-0.009	72	67	62	36			
	6205		60 80	20		55		13	96	66		48	62	-0.010	80	73	70	40			
	6806		70 80	20		62		16	104	74		55	70	-0.040	88	79	77	44			
	6906		70 80	20		62		14	104	74		55	70		88	79	75	44			
	6006		70 90	20	35	72	+0.030	17	126	88	20	64	84	-0.010	105	95	92	51	17.5	11	11
	6207		80 90	20		68	0	15	114	82	13	60	78	-0.010	96	86	80	54	14	9	8.1
	6008		70 90	20		80		18	134	96		74	92	-0.010	113	102	98	56			
	6208		80 90	20	40	80		16	134	96		74	92	-0.012	113	—	98	56	17.5	11	11
	6010		80 90	20	50	80		20	147	110		83	106	-0.047	126	—	104	72			
	6210	ZZ (両シールド)	100	20		90	+0.035	20	147	110		83	106		126	—	104	72			

適用サイズは価格表でご確認ください。*VV(非接触ゴムシール)は67番台・623番・624番・605番・606番は選択できません。
 ※1印：2008年度初版カタログ記載ミスの訂正した箇所になります。

<訂正用>

25
20
20
20

適用サイズは価格表でご確認ください。*VV(非接触ゴムシール)は67番台・623番・624番・605番・606番は選択できません。
 ※1印：2008年度初版カタログ記載ミスの訂正した箇所になります。