

P873 (規格表)

赤枠内 数値を一部変更

Catalog No.		L選択				d ₁	B	ℓ	S	耐荷重 (kN)	質量 (g)	¥単価 1~9本		
Type	M(並目)											RSM	RSU	
RSM RSU (ステンレス)	3	5.2	10.2			1.5	1.5	1.2	0.5	0.5	0.2 ~ 0.4	230	350	
	4	6.5	10.5	16.5		2.5	2	2	0.8	1.3	0.4 ~ 1	130	180	
	5	8.6	12.6	20.6		3	2.5		1	1.4	0.8 ~ 2.3			
	6	10.8	16.8	20.8	25.8		4	3	3.5	1.3	3.3	1.5 ~ 4		
	8	(11.2)	13.2	21.2	26.2	31.2	5.6	4	5 (2.5)	1.8	3.9	2.5 ~ 9	140	220
	10	(13.7)	17.7	21.7	26.7	36.7	7.1	5	6 (3.5)	2.3	3.4	5 ~ 16	160	280
	12	(18)	22	32	42		8.7	6	8 (3)	2.8	4.8	10 ~ 28	220	400
	16	(23.3)	38.3	53.3			11.9	8	10 (3)	4.3	8.9	22 ~ 48	360	800

⚠ () の付いたLサイズのℓは()寸法になります。

<訂正用>

25.8
26.2
26.7
42