

## RDJEの価格変更

Catalog No.		¥単価 1~4本					
Type	D	最短L~100	L101~200	L201~400	L401~600	L601~800	
RDJN	3	180	310	530	—	—	
	4	180	310	530			
	5	180	310	530			
	6	200	340	590	780		
	8	260	430	740	980		
	10	340	590	1,000	1,330		
	12	480	850	1,460	1,940		2,440
	13	610	1,050	1,810	2,400		2,990
	15	790	1,390	2,380	3,190		3,970
	16	810	1,420	2,450	3,270		4,080
	18	1,140	2,000	3,410	4,540		5,680
	20	1,310	2,310	3,970	5,300		6,630
	25	1,860	3,250	5,580	7,430		9,280
30	2,490	4,370	7,480	9,980	12,480		
RDJF	3	240	430	720	—	—	
	4	240	430	720			
	5	240	430	720			
	6	320	590	980	1,310		
	8	410	720	1,250	1,660		
	10	500	880	1,510	2,010		
	12	620	1,090	1,880	2,510		3,140
	13	720	1,290	2,190	2,920		3,660
	15	970	1,700	2,920	3,900		4,880
	16	1,110	1,940	3,340	4,460		5,580
	18	1,460	2,560	4,390	5,850		7,330
	20	1,740	3,050	5,230	6,980		8,730
	25	2,700	4,740	8,110	10,820		13,530
	30	3,840	6,720	11,520	15,360		19,200
	40	7,370	12,900	22,110	29,480		36,860
50	11,250	19,690	33,750	45,000	56,260		
RDJP	3	890	1,530	2,500	—	—	
	4	890	1,530	2,500			
	5	890	1,530	2,500			
	6	890	1,530	2,500	3,390		
	8	1,370	2,420	4,120	5,490		
	10	1,860	3,230	5,490	7,270		
	12	2,910	5,170	8,730	11,640		14,550
	13	4,390	7,760	13,250	17,620		21,980
	15	4,390	7,760	13,250	17,620		21,980
	16	4,390	7,760	13,250	17,620		21,980
	18	6,140	10,830	18,430	24,570		30,710
	20	6,790	11,960	20,370	27,160		33,950
	25	8,500	14,920	25,530	34,040		42,550
30	13,350	23,360	40,070	53,420	66,780		
RDJE	3	270	480	810	—	—	
	4	270	480	810			
	5	270	480	810			
	6	310	550	940	1,250		
	8	530	940	1,600	2,120		
	10	690	1,220	2,090	2,790		
	12	900	1,580	2,720	3,620		4,530
	13	1,220	2,140	3,660	4,880		6,110
	15	1,570	2,730	4,710	6,240		7,790
	16	1,980	3,490	5,970	7,950		9,950
	18	2,120	3,730	6,390	8,510		10,650
	20	2,260	3,970	6,800	9,070		11,340
	25	4,530	7,940	13,620	18,150		22,690
30	5,130	8,990	15,390	20,520	25,660		
RDJU	3	260	460	780	—	—	
	4	260	460	780			
	5	260	460	780			
	6	290	520	880	1,180		
	8	410	720	1,250	1,660		
	10	440	790	1,350	1,810		
	12	550	970	1,660	2,230		2,790
	13	760	1,330	2,290	3,060		3,840
	15	1,040	1,830	3,140	4,190		5,230
	16	1,390	2,440	4,190	5,580		6,980
	18	1,460	2,560	4,390	5,850		7,330
	20	1,530	2,680	4,600	6,140		7,680
	25	1,980	3,490	5,960	7,950		9,950
30	2,790	4,880	8,380	11,170	13,960		

&lt;訂正用&gt;

RDJE	8	530	940	1,600	2,120	—	
	10	690	1,220	2,090	2,790		
	12	900	1,580	2,720	3,620		4,530
	13	1,220	2,140	3,660	4,880		6,110
	15	1,570	2,730	4,710	6,240		7,790
	16	1,980	3,490	5,970	7,950		9,950
	18	2,120	3,730	6,390	8,510		10,650
	20	2,260	3,970	6,800	9,070		11,340
	25	4,530	7,940	13,620	18,150		22,690
30	5,130	8,990	15,390	20,520	25,660		