

P.1144 (規格表)

C寸に移動量追加

型式		A1	H	C±S(移動量)		F	K	J	D	G	N	W	t	P	Q	X	Y	y	Z	d1	d2
Type	A			マイクロメータ	送りねじ																
ZPG ZPCG ZPBG	*25	25	12.5	37±3.2	23±3.2	11	22.5	6.8	9.3	12.5	15	20	5	6	4.5	20	10	2.5	22.5	2.5	—
	40	50	35	58.5±6.5	55±6.5	24	47	6.5	13	17	20	30	4	10	5.5	32	16	4	30	3.5	6
	60	70	20	58.5±6.5	55±6.5	24	37.5	6.5	13	17	20	45	7	10	5.5	50	25	5	35	4.5	8
	80	80	20	96±12.5	55±6.5	24	45	11.5	18	16.5	20	45	7	10	5.5	50	25	5	35	4.5	8

⊗*ZPBGはA25適用不可

<訂正用>

C±S(移動量)	
マイクロメータ	送りねじ
37±3.2	23±3.2
58.5±6.5	55±6.5
58.5±6.5	55±6.5
96±12.5	55±6.5