

フランジインローフランジタイプD30のF寸数値訂正

型式																	¥単価 1~4コ										
Type	DH7	A	B	H	D1	T	E	d1	d2	h	F	W	b	P _{h7}	S	支柱取付ボルト	PFPB	PFPM	PFPA	PFSS	KFPB	KFPM	KFPSS				
(フランジ) PFPB PFPM PFPA PFSS (インローフランジ) KFPB KFPM KFPSS	6	28	12	16	12	5	9	3.5	6.5	3.5	20	—	3.5	12	5	M 3	870	960	—	1,980	1,520	1,650	3,240				
	8	32	15	22	15		12	4.5	8	4.5	24	—	4.5	15		M 4	890	980	—	2,050	1,520	1,650	3,320				
	10	38	18	26	18		15	5.5	9.5	5.5	30	—	4.5	18		M 5	950	1,070	1,360	2,260	1,610	1,770	3,620				
	12	42	20	32	20	8	18	6.6	11	6.5	32	—	5.5	20		M 6	1,080	1,200	1,750	2,370	1,670	1,830	3,780				
	13																		—					1,780	1,940	3,780	
	15	48	32	40	25	10	23	9	14	9	32	20	6.6	30		M 8	1,220	1,360	2,190	3,270	1,870	2,040	4,990				
	16						31	11	18	11	35	25							2,190					1,980	2,190	4,990	
	20	55	38	50	30	15	38	14	20	14	45	35	9	38		M10	1,360	1,520	2,920	4,300	2,140	2,350	6,740				
	25	75	50	62	38		45	40	M12	1,650	1,840	4,310												5,610	2,490	2,750	9,090
	30	80	55	75	45		45	40																			

<訂正用>

F
20
24
30
32
32
35
45
50