

P.1287 (規格表)

PIJC89のとき、t寸の数値は6.0となります。

型式 Type	D 選択	D 公差	L 指定1mm単位	t	t 公差	¥単価 1~4本					
						L50~100	L101~200	L201~400	L401~600	L601~800	L801~1000
PIJC	13	±0.2	50~1000	2.0	±0.2	660	910	1,410	2,160	2,580	3,000
	18					830	1,160	1,750	2,750	3,330	3,830
	22					910	1,330	1,910	3,000	3,580	4,160
	26	±0.3		2.5	±0.3	1,000	1,500	2,160	3,330	4,000	4,660
	32					1,160	1,750	2,500	3,910	4,750	5,500
	34					1,250	1,910	2,750	4,250	5,160	6,000
	38	±0.4		3.0	±0.4	1,580	2,330	3,410	5,330	6,410	7,500
	42					1,750	2,580	3,830	6,000	7,250	8,500
	48					2,160	3,250	4,750	7,410	9,000	10,500
	60	±0.4		4.0	±0.4	2,500	3,710	5,500	8,570	10,350	12,140
	76					3,350	5,000	7,420	11,570	14,000	16,420
	89					4,070	6,070	9,070	14,000	17,140	20,000

<訂正用>

6.0