

SNFK1.5S 価格変更

Catalog No.		D	d	A	B	L	¥単価 SNFR		¥単価 SNFRS	
Type	No.						1~9コ	10コ~	1~9コ	10コ~
SNFRS	8A	13.8	10.5	34.0	27.5	17.0	—	—	1,200	980
	10A	17.3	14.0				—	—	1,200	980
	15A	21.7	17.5				—	—	1,200	980
SNFR SNFRS	1S	25.4	23	50.5	43.4	21.0	730	580	860	690
	1.5S	38.1	35.7	50.5	43.4		740	590	870	700
	2S	50.8	47.8	64.0	56.4		870	700	1,030	820
	2.5S	63.5	59.5	77.5	70.4		1,220	980	1,520	1,220
	3S	76.3	72.3	91.0	83.4		1,600	1,280	1,940	1,550

Catalog No.		D	A	B	L	¥単価	
Type	No.					1~9コ	10コ~
SNFK	1S	38.1	50.5	43.4	11.0	1,550	1,270
	1.5S	38.1	50.5	43.4		1,550	1,270
	2S	50.8	64.0	56.4		1,760	1,510
	2.5S	63.5	77.5	70.4		2,240	1,950
	3S	76.3	91.0	83.4		2,790	2,510

Catalog No.		D	d	A	B	H ₁	H ₂	¥単価 SNFE		¥単価 SNFES	
Type	No.							1~9コ	10~19コ	1~9コ	10~19コ
SNFE SNFES	1S	25.4	23	50.5	43.4	34	55	2,640	2,240	3,140	2,730
	1.5S	38.1	35.7	50.5	43.4	49	70	2,960	2,520	3,710	3,230
	2S	50.8	47.8	64.0	56.4	61	82	3,520	2,990	4,790	4,170
	2.5S	63.5	59.5	77.5	70.4	84	105	5,400	4,590	7,290	6,340
	3S	76.3	72.3	91.0	83.4	89	110	7,200	6,120	8,930	7,770

<訂正用>

1~9コ
1,550
1,550
1,760
2,240
2,790