

規格表下の注釈追加

型式			*Rc (PT), NPT選択	ピッチP		ピッチ数	ポート ねじ数	A	B	E	X	Y	取り付け穴寸法						
Type	取付穴形状変更	No.	R・S	固定タイプ	指定タイプmm単位	N							d	D	h	M	D ₁	d ₁	h ₁
(20角)		1				0	2												
ピッチ固定	ピッチ指定	2				1	4												
BTSB	BTSBP	3	1 (1/8)	25	15~50	2	6	20	20	20	7.5	10	5.5	9.5	5.5	M5	8	4.2 (4.3)	4.5
BTSBM	BTSBMP	4				3	8												
BTSBR	BTSBRP	5				4	10												
		6				5	12												
⑦d ₁ の寸法()はSUS304のみ																			
(30×35角)		1				0	2												
ピッチ固定	ピッチ指定	2	1 (1/8)			1	4												
BTS	BTSP	3	2 (1/4)	35	25~50	2	6	30	35	20	7.5	17.5	6.6	11	6.5	M6	9.5	5.1	5.5
BTSM	BTSMMP	4	3 (3/8)			3	8												
BTSR	BTSRMP	5	1N (NPT1/8)			4	10												
BTSS	BTSSP	6	2N (NPT1/4)			5	12												
BTSC	BTSCP		3N (NPT3/8)																
BTSSJ	BTSSJP																		
(50角)		1				0	2												
ピッチ固定	ピッチ指定	2	2 (1/4)	60	35~60	1	4												
BTSFL	BTSFLP	3	3 (3/8)			2	6	50	50	30	7.5	25	8.5	14	8.5	M8	11	6.8	6.5
BTSFLM	BTSFLMP	4	4 (1/2)			3	8												
BTSFLR	BTSFLRP	5	6 (3/4)			4	10												
BTSFLS	BTSFLSP	6				5	12												
(60角)		1				0	2												
ピッチ固定	ピッチ指定	2	6 (3/4)	60	40~60	1	4	60	60	40	10	30	8.5	14	8.5	M8	11	6.8	6.5
BTSL	BTSLP	3	8 (1)			2	6												
BTSLM	BTSLMP	4				3	8												

⑦印R・Sは()の前の1・2・3・4・6・8・1N・2N・3NのNo.で指定ください。

⑦ピッチ指定タイプはNo.1を選択できません。

⑦BTSJのR・Sは1・2・3のみ指定できます。

⑦ピッチを指定する場合には継手の取付に必要な寸法にご注意ください。

⑦No.6の場合のみL/2の位置にも取り付け穴があります。

⑦20角の場合を除く