

形状選択L寸指定タイプの形状QのLminの訂正

型式			L 指定1mm単位	M 選択	テーパタイプのみ		R	ℓ	W
Type	形状	D			E 指定0.5mm単位	A 指定1 単位			
JPFJ (ポリアセタール) JPFM (MCナイロン導電性CDR2) JPFMC (MCナイロン) JFPF (PEEK)	F R Q* T	6	10 (17) ~ 50	3	$5.0 \leq E$ $E \leq M \times 3$	$1 \sim 45^\circ$	1	8	5
		8	12 (19) ~ 50	3 4			1.5		7
		10	15 (22) ~ 50	3 4 5			2		8
		12	16 (27) ~ 100	4 5 6			$10S$ 10 $12S$ 12	15 $15S$ 17	10
		15	20 (35) ~ 100	5 6 8S 8					14
		16	20 (35) ~ 100	6 8S 8					17
		18	25 (40) ~ 100	6 8S 8 10S 10 12S 12					20 $20S$ 27
		20	25 (40) ~ 100	8S 8 10S 10 12S 12			27 $27S$ 37		
		30	35 (63) ~ 100	10S 10 12S 12 14S 18S					
		40	45 (87) ~ 100	10S 10 12S 12 14S 18S					

<訂正用>

10 (17) ~ 50
12 (19) ~ 50
15 (22) ~ 50
16 (27) ~ 100
20 (35) ~ 100
25 (40) ~ 100
35 (63) ~ 100
45 (87) ~ 100