

P.1920 (規格表)

枠内 赤文字表記部を修正

Catalog No.		L	L ₁	H	D	d	a	P	耐荷重N (kgf)		¥単価 1~29コ
Type	M								BCHM	BCHMJ	
BCHM (ステンレス球)	10	12	2.5	10	18.5	8.73	2	15.4	55 (5.6)	34 (3.5)	990
	12	15	3.5	11	22	10.32		18.5	62 (6.3)	55 (5.6)	1,110
BCHMJ (ポリアセタール球)	16	20	5.3	15	27	15.87	2.5	24	84 (35)	69 (7)	1,320
	20	25	6.3	18	33	19.05		29.6	112 (42)	82 (8.4)	1,710

kgf=N×0.101972

<訂正用>

P
15.4
18.5
24
29.6