

スパナ溝寸法範囲を下記に修正

■両端めねじパイプタイプ

Catalog No.			スパナ溝寸法			d	C	
Type	Dg6		SC	W	ℓ_1			
両端めねじパイプタイプ SPJW SSPJW (*サイズのみ) PSPJW	6	—0.004 —0.012	SC=指定1mm単位 Ⓢ D \leq 25の場合 SC+ $\ell_1 \leq L-N \times 2$ SC $\geq M \times 2$ Ⓢ D \geq 30の場合 SC+ $\ell_1 \leq L$ SC=0または SC \geq 1	5	8	2	0.5 以下	
	* 8	—0.005		7		3(3)		
	* 10	—0.014		8		4(4)		
	* 12	—0.006		10	6(5)			
	* 13	—0.017		11	7(5)			
	* 16	—0.017		14	10	10(6)		
	両端めねじパイプ スパナ溝付きタイプ SPWR SSPWR (*サイズのみ) PSPWR	* 20		—0.007	17	10	14(8)	1.0 以下
		* 25		—0.020	22	10	16(10)	
		* 30		—0.020	27	15	17(12)	
		35		—0.009	30	15	19	
40		—0.025	36	20	20			
50		—0.025	41	20	26			
			Ⓢ スパナ溝詳細 P.92					