

赤枠内変更

表1：軸穴径選択

| d _{H7} | 最大許容トルク N・m | D | (L) | 呼び幅 | | | |
|-----------------|----------------|----|------|--------|--------|--------|--------|
| | | | | T10150 | T10200 | T10250 | T10300 |
| 12 | 48 | 32 | 10.5 | ○ | ○ | ● | — |
| 14 | 73 | 35 | 12 | ○ | ○ | ● | — |
| 15 | 78 | 36 | | ○ | ○ | ● | ● |
| 16 | 83 | 37 | 13 | ○ | ○ | ● | ● |
| 17 | 88 | 38 | | ○ | ○ | ● | ● |
| 18 | 154 | 43 | 14 | ○ | ○ | ● | ● |
| 19 | 163 | 45 | | ○ | ○ | ● | ● |
| 20 | 171 | 46 | | ○ | ○ | ● | ● |
| 22 | 186 | 48 | | ○ | ○ | ● | ● |
| 24 | 206 | 50 | | ○ | ○ | ● | ● |
| 25 | 216 | 52 | | ○ | ○ | ● | ● |
| 28 | 353 | 54 | 15.5 | ○ | ○ | ● | ● |
| 30 | 382 | 57 | | ○ | ○ | ● | ● |
| 32 | 412 | 59 | 16.5 | ○ | ○ | ○ | ● |
| 35 | 451 | 63 | | ○ | ○ | ○ | ○ |
| 38 | 686 | 70 | 19 | ○ | ○ | ○ | ○ |
| 40 | 725 | 71 | | ○ | ○ | ○ | ○ |
| 42 | 757 | 74 | 20 | ○ | ○ | ○ | ○ |
| 45 | 1490 | 84 | 24.5 | ○ | ○ | ○ | ○ |
| 48 | 1600 | 87 | | ○ | ○ | ○ | ○ |
| 50 | 1660 | 89 | | ○ | ○ | ○ | ○ |

○印は E 形のみ適用範囲です。

●印は E F 形適用範囲です。