

GRRMG価格を赤字のように訂正

Catalog No.		A 選択	S 選択	W	T	X	Y	d1	d2	h	¥単価 1~4コ					
Type	B										GRR	GRRM	GRRG	GRRMG	GRMZ	GRRP
(スタンダードタイプ) GRR GRRM	15	40	5	5	10	5	5	8	4.5	4.5	3,400	3,820	3,650	4,070	2,160	1,170
		60									3,600	4,020	3,900	4,320	2,700	1,280
		80									3,800	4,220	4,150	4,570	3,160	1,400
		100									4,000	4,420	4,450	4,870	3,940	1,630
		120*									4,200	4,620	4,750	5,170	4,580	1,870
(油溝付タイプ) GRRG GRRMG	20	60	8 10	5	15	7	7	9.5	5.5	5.5	3,600	4,100	3,900	4,400	3,160	1,280
		80									3,800	4,300	4,150	4,650	3,900	1,520
		100									4,030	4,530	4,480	4,980	4,760	1,870
		120									4,280	4,780	4,830	5,330	5,500	2,100
		150									4,530	5,030	5,180	5,680	7,040	2,220
(銅合金タイプ) GRMZ	25	80	10 12 15	5	20	10	10	11	6.5	6.5	3,800	4,470	4,200	4,870	5,480	1,750
		100									4,100	4,770	4,600	5,270	6,680	2,100
		120									4,370	5,030	4,970	5,630	7,820	2,450
		150									4,550	5,220	5,250	5,920	8,530	2,920
		200									4,850	5,520	5,750	6,420	11,800	3,500
(樹脂タイプ) GRRP	30	80	12 15 20	8	25	10	10	14	9	9	5,950	6,620	6,450	7,120	7,240	2,100
		100									6,250	6,920	6,850	7,520	8,980	2,450
		120									6,680	7,520	7,380	8,190	10,580	2,920
		150									6,970	7,970	7,770	8,770	11,200	3,500
		200									7,580	8,580	8,680	9,680	14,370	4,200

* 15-120-5の取付ボルト穴数は3コになります。