

P.943 <規格表>

吸着力N数値を追加。

Catalog No.		A	B	*吸着力 N (kgf)	表面磁束密度 ガウス[G]	¥単価 1~9コ
Type	T					
MGLN (ネオジム磁石)	1	10	5	2.7 (0.28)	1800	650
	2	10	10	11.8 (1.20)	2600	780
	3	15	5	13.9 (1.42)	3200	800
	5	15	10	34.3 (3.50)	3300~3700	980
		20	15	69.7 (7.11)		1,200
		30	30	179.7 (18.32)		1,900

Catalog No.		A	B	*吸着力 N (kgf)	表面磁束密度 ガウス[G]	¥単価 1~9コ
Type	T					
MGLF (フェライト磁石)	5	10	5	1.6 (0.16)	1000	390
		20	10	4.9 (0.50)	1100	390
		30	20	9.8 (1.00)		450
		*50	20	12.7 (1.30)		450
	10	30	30	21.6 (2.20)	1300	680
		*30	60	29.4 (3.00)		980
		20	20	17.7 (1.80)		680
		*40	40	31.4 (3.20)		980