

赤枠内 B寸法を修正

Catalog No.			P.D.	O.D.	F	E	A	W	S	ペアリング寸法				使用止め輪		¥単価 1~4コ					
Type	歯数	対応ベルト								No.	d	D	B	AHTF KHTF NHTF MHTF SHTF	BHTF	AHTF	KHTF	NHTF	BHTF	MHTF	SHTF
AHTF KHTF NHTF BHTF MHTF SHTF	20	S3M060	19.10	18.34	22	14	7	11	3	685ZZ×1	5	11	5	RTWS11	RTWN11	2,180	2,390	2,610	—	—	—
		S3M100					11	15	2.5	685ZZ×2						2,660	2,920	3,190	—	—	—
	24	S3M060	22.92	22.16	25	16	7	11	3.5	695ZZ×1	5	13	4	RTWS13	RTWN13	2,270	2,490	2,720	2,180	2,450	2,590
		S3M100					11	15	3.5	695ZZ×2						2,720	2,990	3,260	2,620	2,890	3,080
	25	S3M060	23.87	23.11	28	18	7	11	3.5	695ZZ×1	5	13	4	RTWS13	RTWN13	2,380	2,610	2,850	2,330	2,560	—
	26	S3M060	24.83	24.07	28	18	7	11	3	696ZZ×1	6	15	5	RTWS15	RTWN15	2,480	2,720	2,970	2,430	2,670	—
	28	S3M060	26.74	25.98	30	20	7	11	3	696ZZ×1	6	15	5	RTWS15	RTWN15	2,500	2,750	3,000	2,450	2,690	—
	30	S3M060	28.65	27.89	32	23	7	11	3	696ZZ×1	6	15	5	RTWS15	RTWN15	2,520	2,770	3,020	2,450	2,720	2,950
		S3M100					11	15	4.5	626ZZ×1						2,790	3,060	3,340	2,720	2,990	3,270
	32	S3M060	30.56	29.80	35	25	7	11	2.5	698ZZ×1	8	19	6	RTWS19	RTWN19	2,970	3,260	3,560	2,900	3,170	3,490
		S3M100					11	15	4.5							3,060	3,360	3,670	2,990	3,260	3,600
	36	S3M060	34.38	33.62	40	28	7	11	2.5	698ZZ×1	8	19	6	RTWS19	RTWN19	3,350	3,680	4,020	3,280	3,600	—
	40	S3M060	38.20	37.44	44	32	7	11	2.5	6900ZZ×1	10	22	6	RTWS22	RTWN22	3,610	3,970	4,330	3,530	3,880	—
	44	S3M060	42.02	41.25	48	36	7	11	2.5	6900ZZ×1	10	22	6	RTWS22	RTWN22	3,860	4,240	4,630	—	—	—
48	S3M060	45.84	45.07	50	38	7	11	2.5	6900ZZ×1	10	22	6	RTWS24	RTWN24	3,920	4,310	4,700	—	—	—	
50	S3M060	47.75	46.98	52	40	7	11	2.5	6900ZZ×1	10	22	6	RTWS22	RTWN22	4,050	4,450	4,860	3,960	4,350	—	
60	S3M060	57.30	56.53	61	46	7	11	2.5	6900ZZ×1	10	22	6	RTWS22	RTWN22	4,730	5,200	5,670	4,630	5,090	—	

&lt;訂正用&gt;

3
2.5