

- ①精密級の指定単位の訂正
- ②価格の訂正

■L寸指定タイプ-並級・精密級-

型式		D 選択	L 指定 並級0.5mm単位 精密級0.1mm単位	改定価格 ¥単価 1~4コ													
Type	V			並級								精密級					
				NCLC	NCLM	NCLB NCLCH	NCLA NCLBH	NCLMH	NCLSS	NCLSSH	ACSC	AMSC	ABSC ASH	AASC ASC	PASC	SASC	SASCH
-並級- NCLC NCLB NCLM NCLA NCLSS NCLCH NCLBH NCLMH NCLSSH	2	4 5 6 8 10	10.0 ~ 16.0	150	180	160	190	210	250	320	240	270	260	290	310	370	410
	3	5 6 8 10 12	10.0 ~ 25.0	150	180	160	190	210	250	320	240	270	260	290	310	370	410
			25.1 ~ 50.0	160	190	170	200	230	360	390	250	280	270	300	330	450	490
	4 5 6	(6) 8 10 12 13 14 15 16 Ⓢ(6) ...V4に適用 20 25	10.0 ~ 25.0	150	180	160	190	210	390	400	240	270	260	290	310	490	500
			25.1 ~ 50.0	160	190	170	200	230	430	450	260	290	280	310	330	530	550
			10.0 ~ 25.0	160	190	170	200	220	450	470	260	300	280	320	340	560	580
			25.1 ~ 50.0	310	330	320	330	340	500	540	430	450	440	470	460	610	650
	8 10 12	(10) (12) (13) (14) 15 16 Ⓢ(10) ...V8に適用 Ⓢ(12 13 14) ...V8・10に適用 20 25 30 35	10.0 ~ 25.0	200	220	210	250	270	400	410	300	320	310	350	370	500	520
			25.1 ~ 50.0	210	240	250	290	290	450	470	410	340	350	390	400	550	580
			50.1 ~ 75.0	380	400	390	400	410	500	520	480	500	490	500	520	610	640
			75.1 ~ 100.0	490	510	500	510	520	630	680	610	630	620	650	660	770	820
			10.0 ~ 25.0	220	260	230	270	310	500	520	330	360	350	390	430	620	640
25.1 ~ 50.0			360	380	370	380	390	550	580	480	500	490	510	510	670	700	
50.1 ~ 75.0			510	530	520	530	540	780	820	630	650	650	660	670	910	950	
75.1 ~ 100.0			660	680	670	680	690	970	1,080	800	820	810	820	830	1,110	1,220	
10.0 ~ 25.0			350	380	370	380	400	540	580	520	570	550	560	590	700	770	
25.1 ~ 50.0			640	670	660	670	690	1,000	1,080	810	860	840	850	880	1,150	1,270	
50.1 ~ 75.0			930	960	940	960	980	1,460	1,570	1,110	1,170	1,140	1,160	1,180	1,630	1,770	
75.1 ~ 100.0			1,120	1,220	1,200	1,250	1,370	1,910	2,090	1,300	1,430	1,400	1,450	1,570	2,080	2,290	
10 12	40 50 60	10.0 ~ 25.0	610	750	700	780	800	1,360	1,470	780	920	870	960	990	1,540	1,660	
		25.1 ~ 50.0	820	1,050	910	1,150	1,300	2,380	2,580	990	1,220	1,080	1,310	1,490	2,560	2,770	
		50.1 ~ 75.0	1,190	1,400	1,340	1,500	1,850	3,400	3,680	1,370	1,580	1,530	1,690	2,050	3,590	3,880	
		75.1 ~ 100.0	1,350	1,500	1,530	1,750	1,950	4,760	5,150	1,530	1,680	1,720	1,940	2,150	4,950	5,350	
		10.0 ~ 25.0	230	280	250	300	340	530	550	370	420	400	450	490	680	700	
		25.1 ~ 50.0	420	440	430	450	460	610	650	560	590	580	600	610	760	800	
		50.1 ~ 75.0	540	560	540	600	610	860	930	680	710	690	750	760	1,010	1,080	
		75.1 ~ 100.0	750	780	770	790	800	1,150	1,260	890	940	930	950	960	1,300	1,410	
		10.0 ~ 25.0	410	450	430	450	470	630	670	570	600	600	620	640	800	840	
		25.1 ~ 50.0	740	780	760	780	800	1,160	1,250	920	940	930	950	980	1,340	1,430	
		50.1 ~ 75.0	1,080	1,120	1,100	1,120	1,140	1,700	1,810	1,260	1,300	1,280	1,300	1,320	1,880	1,990	
		75.1 ~ 100.0	1,140	1,240	1,220	1,280	1,400	1,950	2,130	1,330	1,460	1,430	1,480	1,600	2,120	2,340	
15 16 20	30 35 40 50 60	10.0 ~ 25.0	640	780	680	810	830	1,390	1,500	810	950	850	990	1,020	1,570	1,690	
		25.1 ~ 50.0	850	1,080	940	1,180	1,330	2,410	2,610	1,020	1,250	1,110	1,360	1,520	2,590	2,800	
		50.1 ~ 75.0	1,210	1,430	1,370	1,530	1,880	3,430	3,710	1,390	1,610	1,560	1,720	2,080	3,620	3,910	
		75.1 ~ 100.0	1,380	1,530	1,560	1,700	1,980	4,790	5,180	1,560	1,710	1,750	1,890	2,180	4,980	5,380	
		10.0 ~ 25.0	440	480	460	480	500	660	700	600	630	630	650	670	830	870	
		25.1 ~ 50.0	770	810	790	810	830	1,190	1,280	950	970	960	980	1,010	1,370	1,460	
		50.1 ~ 75.0	1,110	1,150	1,130	1,150	1,170	1,730	1,840	1,290	1,330	1,310	1,330	1,350	1,910	2,020	
		75.1 ~ 100.0	1,160	1,260	1,240	1,310	1,430	1,990	2,170	1,360	1,490	1,460	1,510	1,630	2,160	2,390	
		10.0 ~ 25.0	670	810	710	840	860	1,420	1,530	840	980	880	1,020	1,050	1,600	1,720	
		25.1 ~ 50.0	880	1,110	970	1,210	1,360	2,440	2,640	1,050	1,280	1,140	1,390	1,550	2,620	2,830	
		50.1 ~ 75.0	1,240	1,460	1,400	1,560	1,910	3,460	3,740	1,420	1,640	1,590	1,750	2,110	3,650	3,940	
		75.1 ~ 100.0	1,410	1,560	1,590	1,700	2,010	4,820	5,210	1,590	1,740	1,780	1,890	2,210	5,010	5,410	

<訂正用>

①

L
指定
並級0.5mm単位
精密級0.1mm単位

②

1,700 1,980 4,790 5,180 1,560 1,710 1,750 1,890