

単価部分 L寸法の最小指定数値は1.01になります。

1

Catalog No.	D	L 指定0.1mm単位	Ds	適用ベアリング	Y単価 1~4コ												
					CLBU・CLBP	CLBUB・CLBPB	CLBUM・CLBPM	CLBUS・CLBPS									
内輪用 (マイナス公差) CLBU CLBUB CLBUM CLBUS (プラス公差) CLBP CLBPB CLBPM CLBPS	3	5	4	673Z2・683Z2・693Z2	180	210	—	280	320	—	300	350	—	330	430	—	
	4	7	6	674Z2・684Z2・694Z2	210	230	—	320	350	—	350	390	—	390	470	—	
	5	8	7	685Z2・695Z2・705Z2	230	250	—	350	380	—	390	420	—	420	510	—	
	6	9	8	696Z2・706Z2・716Z2	250	270	—	380	410	—	420	450	—	460	550	—	
	7	13	12	6800Z2	270	290	—	410	440	—	450	490	—	490	590	—	
	8	11	10	6800Z2	290	310	410	430	460	580	460	520	680	570	690	900	
	10	14	13	6900Z2・6000Z2	300	330	430	460	500	650	500	550	720	670	870	690	900
		17	16	6200Z2	320	350	460	490	530	700	530	580	770	810	730	960	
	12	15	14	6801Z2	320	350	460	490	530	700	520	560	760	810	730	960	
		16	15	6901Z2・6001Z2	320	350	460	490	530	700	530	580	770	810	730	960	
	15	18	17	6201Z2	330	360	470	500	550	710	550	600	780	830	750	980	
		18	17	6802Z2	330	370	480	500	550	720	550	610	790	830	780	1,020	
	17	20	18	6902Z2・6002Z2	330	370	490	500	560	740	550	620	820	830	780	1,020	
		21	20	6202Z2	340	380	510	520	580	770	570	630	850	850	790	1,060	
	20	22	19	6903Z2	340	390	520	520	590	780	570	630	850	850	820	1,080	
		22	21	6903Z2・6003Z2	340	390	520	520	610	790	570	640	860	860	820	1,080	
	25	24	23	6203Z2	370	410	550	540	630	810	580	660	870	700	860	1,140	
		24	23	6804Z2	340	410	540	520	610	790	580	670	870	700	860	1,100	
	30	27	26	6904Z2	350	410	530	530	620	800	580	680	880	660	860	1,100	
		27	26	6904Z2・6204Z2	390	430	570	590	650	860	650	720	950	740	900	1,180	
	35	28	27	6905Z2	390	440	580	600	660	880	660	730	970	780	940	1,240	
		28	27	6905Z2	400	450	600	610	680	910	670	750	1,000	780	940	1,240	
	40	31	30	6906Z2	420	470	620	640	710	940	700	780	1,030	790	980	1,280	
		33	32	6205Z2	420	470	620	640	710	940	700	780	1,030	790	980	1,280	
	45	33	32	6806Z2	430	490	640	640	740	960	710	790	1,050	810	1,040	1,360	
		35	34	6906Z2	430	500	660	650	760	1,000	720	830	1,100	810	1,040	1,360	
	50	38	37	6906Z2	440	520	670	670	790	1,010	730	860	1,110	830	1,080	1,380	
		40	39	6206Z2	450	530	690	680	850	1,120	750	910	1,190	850	1,100	1,420	
	55	38	37	6807Z2	490	580	720	790	890	1,120	760	990	1,230	970	1,230	1,500	
		42	41	6907Z2	520	630	750	790	950	1,130	870	1,050	1,250	1,030	1,300	1,550	
	60	44	43	6907Z2・6207Z2	550	660	790	830	980	1,190	910	1,080	1,310	1,090	1,360	1,630	
		46	45	6808Z2	560	670	810	840	990	1,210	930	1,090	1,330	1,120	1,400	1,710	
	65	43	42	6908Z2	570	680	830	850	1,020	1,230	940	1,120	1,350	1,120	1,400	1,710	
		49	48	6908Z2・6208Z2	610	720	880	890	1,060	1,280	980	1,160	1,400	1,200	1,480	1,810	

2

Catalog No.	D	L 指定0.1mm単位	d	Dh	適用ベアリング	Y単価 1~4コ											
						CLBS・CLBT	CLBSB・CLBTB	CLBSM・CLBTM	CLBS5・CLBT5								
外輪用 (マイナス公差) CLBS CLBSB CLBSM CLBS5 (プラス公差) CLBT CLBTB CLBTM CLBT5	6	7	4	5	673Z2	200	240	—	310	370	—	340	400	—	370	490	—
	7	8	5	6	674Z2	210	260	—	320	400	—	350	440	—	390	530	—
	8	9	5	6	683Z2	220	270	—	340	410	—	370	450	—	400	550	—
	10	11	7	8	623Z2	230	280	—	350	430	—	390	470	—	420	560	—
	11	13	7	8	694Z2	240	290	—	370	440	—	400	490	—	440	580	—
	13	14	9	10	624Z2・685Z2	260	310	—	400	470	—	440	520	—	500	650	—
	14	15	10	11	695Z2	270	330	—	410	500	—	450	550	—	520	690	—
	15	16	10	11	696Z2	290	350	—	440	530	—	490	580	—	560	730	—
	16	17	11	12	625Z2	300	360	—	460	550	—	500	600	—	570	750	—
	17	19	12	13	6806Z2	320	380	—	490	580	—	530	630	—	610	790	—
	19A	14	15	15	626Z2・698Z2	330	400	—	500	610	—	560	670	—	630	840	—
		21	18	19	6901Z2	330	400	—	510	620	730	560	680	760	630	840	1,000
	21	18	19	6901Z2	340	410	490	520	630	750	570	690	800	660	880	1,040	
	22	17	18	6902Z2・6901Z2	350	420	500	530	640	760	580	700	830	660	880	1,040	
	24	19	20	628Z2・6901Z2	370	440	530	560	670	800	620	730	880	700	920	1,100	
	24A	21	22	6902Z2	380	460	550	570	690	820	640	760	900	740	980	1,160	
	26	20	21	6900Z2	390	470	560	590	710	850	650	780	930	740	980	1,160	
	26A	23	24	6903Z2	400	480	580	610	730	870	670	800	960	740	980	1,160	
	28	22	23	6901Z2・6902Z2	410	490	590	620	740	890	680	820	980	780	1,020	1,220	
	30	24	25	6200Z2	430	510	620	650	770	940	720	850	1,030	810	1,060	1,280	
	32	25	26	6201Z2・6002Z2	450	540	650	680	820	980	750	900	1,080	850	1,120	1,340	
	32A	29	30	6804Z2	460	560	670	700	840	1,010	760	930	1,100	870	1,150	1,370	
	35	29	30	6202Z2	470	570	680	710	860	1,030	780	950	1,130	890	1,180	1,400	
	37	31	32	6904Z2	500	600	720	760	910	1,090	830	1,000	1,190	940	1,240	1,660	
	37A	34	35	6905Z2	510	620	740	780	930	1,110	850	1,030	1,220	980	1,300	1,550	
	42	34	35	6904Z2・6905Z2	520	630	750	790	950	1,130	860	1,050	1,240	980	1,300	1,550	
	47	39	40	6906Z2	530	650	770	810	980	1,160	890	1,090	1,290	1,090	1,360	1,630	
	47A	39	40	6204Z2・6905Z2・6906Z2	550	680	790	830	1,000	1,190	910	1,100	1,310	1,090	1,360	1,630	
	52	44	45	6907Z2	670	800	910	950	1,130	1,320	940	1,130	1,360	1,120	1,400	1,670	
	52A	45	46	6205Z2	580	690	830	880	1,040	1,250	960	1,150	1,380	1,140	1,420	1,710	
	55	49	50	6908Z2	600	710	860	920	1,140	1,450	980	1,270	1,580	1,200	1,500	1,810	
	55A	46	47	6906Z2	610	730	880	940	1,190	1,510	1,020	1,300	1,640	1,200	1,500	1,810	
	62	55	56	6206Z2・6907Z2・6908Z2	640	770	920	990	1,280	1,600	1,090	1,410	1,740	1,260	1,590	1,890	
	70	63	64	6207Z2・6908Z2・6208Z2	790	950	1,140	1,140	1,460	1,810	1,240	1,590	1,950	1,550	1,950	2,330	

<訂正用>

1

Y単価 1~4コ			
CLBU・CLBP	CLBUB・CLBPB	CLBUM・CLBPM	CLBUS・CLBPS
1.10-25.0	25.1-50.0	50.1-100.0	1.10-25.0
25.1-50.0	50.1-100.0	1.10-25.0	25.1-50.0
50.1-100.0	1.10-25.0	25.1-50.0	50.1-100.0

2

Y単価 1~4コ			
CLBS・CLBT	CLBSB・CLBTB	CLBSM・CLBTM	CLBS5・CLBT5
1.10-25.0	25.1-50.0	50.1-100.0	1.10-25.0
25.1-50.0	50.1-100.0	1.10-25.0	25.1-50.0
50.1-100.0	1.10-25.0	25.1-50.0	50.1-100.0