

SWRタイプのD10.5の型番訂正

| D | d | L | N/mm (kgf/mm) (ばね定数) | | φmin (標準長) | F=L×50% | | 型式 Type D-L | ¥単価 | |
|------|------|------|-------------------------|---------------|---------------|---------|-----------------|----------------|-----|-----|
| | | | Fmm | N (kgf/mm) | | 1~19本 | 1~19本 | | | |
| 10.5 | 6.0 | 15 | 10.46 | 1.07 | 6.0 | 7.5 | 78.5 (8.0) | SWR10.5- | 15 | 90 |
| | | 20 | 7.85 | 0.80 | 8.0 | 10.0 | | 20 | 90 | |
| | | 25 | 6.28 | 0.64 | 10.0 | 12.5 | | 25 | 95 | |
| | | 30 | 5.23 | 0.53 | 12.0 | 15.0 | | 30 | 100 | |
| | | 35 | 4.48 | 0.46 | 14.0 | 17.5 | | 35 | 110 | |
| | | 40 | 3.92 | 0.40 | 16.0 | 20.0 | | 40 | 120 | |
| | | 45 | 3.49 | 0.36 | 18.0 | 22.5 | | 45 | 120 | |
| | | 50 | 3.14 | 0.32 | 20.0 | 25.0 | | 50 | 130 | |
| | | 55 | 2.85 | 0.29 | 22.0 | 27.5 | | 55 | 140 | |
| | | 60 | 2.62 | 0.27 | 24.0 | 30.0 | | 60 | 150 | |
| | | 65 | 2.41 | 0.25 | 26.0 | 32.5 | | 65 | 160 | |
| | | 70 | 2.24 | 0.23 | 28.0 | 35.0 | | 70 | 170 | |
| 75 | 2.09 | 0.21 | 30.0 | 37.5 | 75 | 180 | | | | |
| 80 | 1.96 | 0.20 | 32.0 | 40.0 | 80 | 190 | | | | |
| 12.5 | 7.0 | 15 | 11.77 | 1.20 | 6.0 | 7.5 | 88.3 (9.0) | SWR12.5- | 15 | 95 |
| | | 20 | 8.83 | 0.90 | 8.0 | 10.0 | | 20 | 95 | |
| | | 25 | 7.06 | 0.72 | 10.0 | 12.5 | | 25 | 100 | |
| | | 30 | 5.88 | 0.60 | 12.0 | 15.0 | | 30 | 110 | |
| | | 35 | 5.04 | 0.51 | 14.0 | 17.5 | | 35 | 120 | |
| | | 40 | 4.41 | 0.45 | 16.0 | 20.0 | | 40 | 130 | |
| | | 45 | 3.92 | 0.40 | 18.0 | 22.5 | | 45 | 140 | |
| | | 50 | 3.53 | 0.36 | 20.0 | 25.0 | | 50 | 150 | |
| | | 55 | 3.21 | 0.33 | 22.0 | 27.5 | | 55 | 160 | |
| | | 60 | 2.94 | 0.30 | 24.0 | 30.0 | | 60 | 170 | |
| | | 65 | 2.72 | 0.28 | 26.0 | 32.5 | | 65 | 180 | |
| | | 70 | 2.52 | 0.26 | 28.0 | 35.0 | | 70 | 190 | |
| 75 | 2.35 | 0.24 | 30.0 | 37.5 | 75 | 195 | | | | |
| 80 | 2.21 | 0.23 | 32.0 | 40.0 | 80 | 205 | | | | |
| 90 | 1.96 | 0.20 | 36.0 | 45.0 | 90 | 225 | | | | |
| 100 | 1.77 | 0.18 | 40.0 | 50.0 | 100 | 245 | | | | |
| 14.5 | 8.5 | 15 | 17.00 | 1.73 | 6.0 | 7.5 | 127.5 (13.0) | SWR14.5- | 15 | 110 |
| | | 20 | 12.75 | 1.30 | 8.0 | 10.0 | | 20 | 120 | |
| | | 25 | 10.20 | 1.04 | 10.0 | 12.5 | | 25 | 130 | |
| | | 30 | 8.50 | 0.87 | 12.0 | 15.0 | | 30 | 140 | |
| | | 35 | 7.28 | 0.74 | 14.0 | 17.5 | | 35 | 150 | |
| | | 40 | 6.37 | 0.65 | 16.0 | 20.0 | | 40 | 160 | |
| | | 45 | 5.67 | 0.58 | 18.0 | 22.5 | | 45 | 170 | |
| | | 50 | 5.10 | 0.52 | 20.0 | 25.0 | | 50 | 180 | |
| | | 55 | 4.64 | 0.47 | 22.0 | 27.5 | | 55 | 185 | |
| | | 60 | 4.25 | 0.43 | 24.0 | 30.0 | | 60 | 190 | |
| | | 65 | 3.92 | 0.40 | 26.0 | 32.5 | | 65 | 200 | |
| | | 70 | 3.64 | 0.37 | 28.0 | 35.0 | | 70 | 210 | |
| | | 75 | 3.40 | 0.35 | 30.0 | 37.5 | | 75 | 220 | |
| | | 80 | 3.19 | 0.33 | 32.0 | 40.0 | | 80 | 230 | |
| 90 | 2.83 | 0.29 | 36.0 | 45.0 | 90 | 250 | | | | |
| 100 | 2.55 | 0.26 | 40.0 | 50.0 | 100 | 270 | | | | |
| 125 | 2.04 | 0.21 | 50.0 | 62.5 | 125 | 290 | | | | |
| 150 | 1.70 | 0.17 | 60.0 | 75.0 | 150 | 310 | | | | |
| 17 | 10.5 | 20 | 19.61 | 2.00 | 8.0 | 10.0 | 196.1 (20.0) | SWR17- | 20 | 130 |
| | | 25 | 15.69 | 1.60 | 10.0 | 12.5 | | 25 | 140 | |
| | | 30 | 13.08 | 1.33 | 12.0 | 15.0 | | 30 | 150 | |
| | | 35 | 11.21 | 1.14 | 14.0 | 17.5 | | 35 | 160 | |
| | | 40 | 9.81 | 1.00 | 16.0 | 20.0 | | 40 | 170 | |
| | | 45 | 8.72 | 0.89 | 18.0 | 22.5 | | 45 | 180 | |
| | | 50 | 7.85 | 0.80 | 20.0 | 25.0 | | 50 | 185 | |
| | | 55 | 7.13 | 0.73 | 22.0 | 27.5 | | 55 | 190 | |
| | | 60 | 6.54 | 0.67 | 24.0 | 30.0 | | 60 | 200 | |
| | | 65 | 6.03 | 0.62 | 26.0 | 32.5 | | 65 | 210 | |
| | | 70 | 5.60 | 0.57 | 28.0 | 35.0 | | 70 | 220 | |
| | | 75 | 5.23 | 0.53 | 30.0 | 37.5 | | 75 | 230 | |
| | | 80 | 4.90 | 0.50 | 32.0 | 40.0 | | 80 | 240 | |
| | | 90 | 4.36 | 0.44 | 36.0 | 45.0 | | 90 | 260 | |
| | | 100 | 3.92 | 0.40 | 40.0 | 50.0 | | 100 | 275 | |
| | | 125 | 3.14 | 0.32 | 50.0 | 62.5 | | 125 | 300 | |
| 150 | 2.62 | 0.27 | 60.0 | 75.0 | 150 | 330 | | | | |
| 175 | 2.24 | 0.23 | 70.0 | 87.5 | 175 | 360 | | | | |

<訂正用>

| | |
|----------|----|
| SWR10.5- | 15 |
| | 20 |
| | 25 |
| | 30 |
| | 35 |
| | 40 |
| | 45 |
| | 50 |
| | 55 |
| | 60 |
| | 65 |
| | 70 |
| | 75 |
| | 80 |