

注文例D寸の前にハイフン追加

■E寸法・R寸法指定範囲詳細

P 指定0.01mm単位	E 指定0.5mm単位	R 選択							
2.00~4.00	1.0~2.0	5	10						
4.01~8.00	2.5~4.0		10	15					
8.01~12.00	4.5~7.0		10	15	20				
12.01~16.00	5.0~10.0			15	20	25			
16.01~20.00	5.0~15.0				20	25	30		
20.01~25.00	5.0~15.0					25	30	35	
25.01~30.00	5.0~20.0						30	35	40

Order 注文例

型式: MGK**FPRB** A M **S** -10 - P12.00 - L10 - B4.0 - E6.0 - R20

Type 形状 D公差 P公差 - D

Delivery 出荷日: 3 日発送

ストーク A 500円/1本 送料 P.92

※同一サイズ3本以上は一律1,350円
※SKS3硬質はストーク適用不可

Price 価格

■数量スライド価格 (¥1円未満切り捨て) P.91

数量	1~4	5~19	20~49	50~99
値引率		5%	10%	15%

※表示数量を超えは別見積り
※バフ研磨品は、20以上からお見積りとなります。

●バフ研磨品(材質No.⑤⑥⑦)

5 日発送

◎精緻の価格
公差選択A・Bを選択した場合は、下記単価×1.1(1円単位切り捨て)
価格算出例
K**FPRBAAB**-10 -P12.00-L10-B5.0-E5.0-R15
1,320(K**FPRBA10**)×1.1=1,450円

■スタンダード

D	¥単価 1~4コ						
	①	②	③	④	⑤	⑥	⑦
	K FPRBA	G KFPRBA	S KFPRBA	C KFPRBA	M KFPRBA	M GKFPRBA	M CKFPRBA
2	890	1,220	1,300	1,470	—	—	—
3	970	1,300	1,390	1,550	—	—	—
4	1,060	1,430	1,510	1,700	—	—	—
5	1,160	1,550	1,640	1,850	1,510	2,020	2,410
6	1,210	1,630	1,720	1,930	1,570	2,120	2,510
8	1,280	1,720	1,820	2,020	1,660	2,240	2,630
10	1,320	1,790	1,900	2,130	1,720	2,330	2,770
12	1,400	1,880	1,980	2,130	1,820	2,440	2,770
13	1,460	1,960	2,080	2,310	1,900	2,550	3,000
16	1,930	2,600	2,770	3,100	2,510	3,380	4,030
20	2,460	3,310	3,510	3,920	3,200	4,300	5,100

■内ねじ

D	¥単価 1~4コ						
	①	②	③	④	⑤	⑥	⑦
	K FPRBTA	G KFPRBTA	S KFPRBTA	C KFPRBTA	M KFPRBTA	M GKFPRBTA	M CKFPRBTA
6	1,480	2,000	2,000	2,210	1,920	2,600	2,870
6T	1,480	2,000	2,000	2,210	1,920	2,600	2,870
8	1,540	2,080	2,090	2,290	2,000	2,700	2,980
8T	1,540	2,080	2,090	2,290	2,000	2,700	2,980
10	1,600	2,150	2,170	2,400	2,080	2,800	3,120
10T	1,570	2,110	2,130	2,350	2,040	2,740	3,060
12	1,670	2,250	2,260	2,400	2,170	2,930	3,120
12T	1,640	2,210	2,210	2,350	2,130	2,870	3,060
13	1,720	2,320	2,340	2,580	2,240	3,020	3,350
13T	1,690	2,270	2,290	2,530	2,200	2,950	3,290
16	2,210	2,970	3,050	3,360	2,870	3,860	4,370
16T	2,170	2,910	2,990	3,290	2,820	3,780	4,280
20	2,720	3,660	3,780	4,190	3,540	4,760	5,450
20T	2,670	3,590	3,700	4,110	3,470	4,670	5,340

■おねじ

D	¥単価 1~4コ						
	①	②	③	④	⑤	⑥	⑦
	K FPRBNA	G KFPRBNA	S KFPRBNA	C KFPRBNA	M KFPRBNA	M GKFPRBNA	M CKFPRBNA
3	1,320	1,780	1,900	2,120	—	—	—
4	1,450	1,960	2,060	2,330	—	—	—
5	1,580	2,120	2,240	2,530	2,050	2,760	3,290
6	1,660	2,230	2,350	2,640	2,160	2,900	3,430
8	1,750	2,350	2,480	2,760	2,280	3,060	3,590
10	1,810	2,450	2,600	2,920	2,350	3,190	3,800
12	1,910	2,570	2,710	2,920	2,480	3,340	3,800
16	2,640	3,560	3,790	4,250	3,430	4,630	5,530
20	3,360	4,540	4,800	5,360	4,370	5,900	6,970

Alteration 追加加工

型式: K**FPRBAMA**-12 - P14.00 - L10 - B3.5 - E5.0 - R15 - RC

5 日発送

	ドライバー溝追加加工	導入部加工	首下R加工	エアークロス加工
Alteration				
Code	DRC	GDC	RC	AC
Spec.	幅0.8mm 深さ1mm ◎おねじのみ適用	導入部を加工します。 指定方法 GDC ◎D=2は適用不可 ◎おねじは適用不可	首下の逃げをR0.5に変更します。 指定方法 RC ◎P-D≥2の場合に適用	エアークロス加工をします。 指定方法 AC ◎おねじは適用不可
¥/1Code	100	200	300	200

<訂正用>

型式: MGK**FPRB** A M **S** -10 - P12.00 - L10 - B4.0 - E6.0 - R20

[K**FPRBAAB**-10 -P12.00-L10-B5.0-E5.0-R15
1,320(K**FPRBA10**)×1.1=1,450円]

型式: K**FPRBAMA**-12 - P14.00 - L10 - B3.5 - E5.0 - R15 - RC